


# Bolt Expansion Anchor, Steel, EG, M16 Rod, 145 mm

## 物料号

**SABM16025**

## 功能



Heavy duty wedge anchor

For cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Approved for use in seismic design category C1 & C2 (for Drill Bit Diameters 8 mm and greater)



## 产品属性

订货号: 402171

材料: 钢

完成: 电镀锌

螺纹尺寸 (TS): M16

长度 (L): 145mm


埋置深度: 97 mm

A: 28 mm

钻头直径: 16mm

| Characteristic Axial Loads from ETA-12/0397 |                         |                             |
|---------------------------------------------|-------------------------|-----------------------------|
| Part Number                                 | Cracked Concrete C20/25 | Non-Cracked Concrete C20/25 |
| SABM8010                                    | 2.4 kN                  | 3.6 kN                      |
| SABM8050                                    | 2.4 kN                  | 3.6 kN                      |
| SABM10010                                   | 4.3 kN                  | 7.6 kN                      |
| SABM10050                                   | 4.3 kN                  | 7.6 kN                      |
| SABM12015                                   | 7.6 kN                  | 11.9 kN                     |
| SABM12050                                   | 7.6 kN                  | 11.9 kN                     |
| SABM16025                                   | 11.9 kN                 | 16.7 kN                     |
| SABM20030                                   | 14.3 kN                 | 23.8 kN                     |
| SABM8010S6                                  | 2.4 kN                  | 4.3 kN                      |
| SABM8050S6                                  | 2.4 kN                  | 4.3 kN                      |
| SABM10010S6                                 | 4.3 kN                  | 7.6 kN                      |
| SABM10050S6                                 | 4.3 kN                  | 7.6 kN                      |

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221  
，按 1 转客户服务  
，按 2 转技术支持

欧洲

荷兰：  
+31 800-0200135  
法国：  
+33 800 901 793

欧洲

德国：  
800 1890272  
其他国家/地区：  
+31 13 5835404

亚太地区

上海：  
+ 86 21 2412 1618/19  
悉尼：  
+61 2 9751 8500

