

Strut Beam Clip, Steel, HDG, 16 mm Max Flange, 13 mm Hole, w/Screw

物料号

ZT605HD

功能


Beam Clip for clamping the open side of strut to a beam

Suitable for all strut channels

Requires installation in pairs

Structural attachment to beams to support nVent CADDY Eristrut

FM® Specification Tested



产品属性

订货号: 313260

材料: 钢

完成: 热浸镀锌

法兰厚度 (FT): 16 mm Max

孔尺寸 (HS): 13 mm

长度 (L): 49mm

厚度 (T): 6 mm



宽度 (W): 40 mm

静态负载: 2040N

包含螺钉: 是

其他产品详情

Indicated loads are based on installation with 1/2" (M12) hardware and strut channel type A.



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

