

HD Heavy Duty Pipe Clamp



功能

Fillet welded connector nut has flats to accommodate spanners

Easy open flange for pipe sizes less than 4"

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

材料: 钢;EPDM-SBR 橡胶

完成: 电镀锌

温度: -50 to 110 °C

颜色: 黑色



技术参数

Table 1/2

物料号	订货号	外径 (OD)	NB/DN	杆尺寸 (RS)	宽度 (W)	厚度 (T)
HDI023	577034	19 - 23 mm	15	M8, M10	30 mm	2.5 mm
HDI028	577035	24 - 28 mm	20	M8, M10	30 mm	2.5 mm
HDI045	577038	40 - 45 mm	32	M8, M10	30 mm	2.5 mm
HDI058	577040	53 - 58 mm		M8, M10	30 mm	2.5 mm
HDI065	577041	60 - 65 mm	50	M8, M10	30 mm	2.5 mm
HDI072	577042	67 - 72 mm		M10, M12	30 mm	3 mm
HDI078	577043	73 - 78 mm	65	M10, M12	30 mm	3 mm
HDI085	577044	79 - 85 mm		M10, M12	30 mm	3 mm
HDI099	577046	94 - 99 mm		M10, M12	30 mm	3 mm

物料号	订货号	外径 (OD)	NB/DN	杆尺寸 (RS)	宽度 (W)	厚度 (T)
HDI106	577047	100 - 106 mm		M10, M12	30 mm	3 mm
HDI116	577048	108 - 116 mm	100	M10, M12	30 mm	3 mm
HDI123	577049	117 - 123 mm		M10, M12	30 mm	3 mm
HDI145	577052	138 - 145 mm	125	M12, M16	40 mm	4 mm
HDI183	577056	177 - 183 mm		M12, M16	40 mm	4 mm
HDI194	577057	188 - 194 mm		M12, M16	40 mm	4 mm
HDI225	577061	219 - 225 mm	200	M16, M20	40 mm	4 mm
HDI236	577063	226 - 236 mm		M16, M20	40 mm	4 mm
HDI261	577065	251 - 261 mm		M16, M20	40 mm	4 mm
HDI273	577066	265 - 273 mm	250	M16, M20	40 mm	4 mm


Table 2/2						
物料号	订货号	螺钉直径 (Sc)	螺钉直径 (公制) (Sc)	螺钉长度 (L)	静态负载	认证
HDI023	577034	6 mm	M6	30mm	2000N	ITB
HDI028	577035	6 mm	M6	30mm	2000N	ITB
HDI045	577038	6 mm	M6	30mm	2000N	ITB
HDI058	577040	6 mm	M6	30mm	2000N	ITB
HDI065	577041	8 mm	M8	40mm	2000N	ITB
HDI072	577042	8 mm	M8	40mm	2000N	
HDI078	577043	8 mm	M8	40mm	3500N	ITB
HDI085	577044	8 mm	M8	40mm	3500N	
HDI099	577046	8 mm	M8	40mm	3500N	
HDI106	577047	8 mm	M8	40mm	3500N	ITB
HDI116	577048	8 mm	M8	40mm	3500N	ITB
HDI123	577049	8 mm	M8	40mm	3500N	ITB
HDI145	577052	10 mm	M10	40mm	5000N	ITB
HDI183	577056	10 mm	M10	40mm	5000N	ITB
HDI194	577057	10 mm	M10	40mm	5000N	
HDI225	577061	12 mm	M12	40mm	10000N	ITB
HDI236	577063	12 mm	M12	40mm	10000N	
HDI261	577065	12 mm	M12	40mm	10000N	ITB

物料号	订货号	螺钉直径 (Sc)	螺钉直径（公制） (Sc)	螺钉长度 (L)	静态负载	认证
HDI273	577066	12 mm	M12	40mm	10000N	ITB

其他产品详情

Lining is EPDM rubber.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

