

nVent CADDY Superfix 243 M8/M10



功能

Includes easy closing mechanism

Combo head bolt works with slotted, hex, or Phillips drivers

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

材料: 钢;EPDM-SBR 橡胶

完成: 电镀锌

颜色: 黑色

温度: -50 to 110 °C



技术参数

Table 1/2


物料号	订货号	外径 (OD)	NB/DN	杆尺寸 (RS)	宽度 (W)	厚度 (T)
SXD014	400063	12 - 14 mm	8	M8, M10	20 mm	1.5 mm
SXD019	400064	15 - 19 mm	10	M8, M10	20 mm	1.5 mm
SXD023	400065	21 - 23 mm	15	M8, M10	20 mm	1.5 mm
SXD028	400066	26 - 28 mm	20	M8, M10	20 mm	1.5 mm
SXD035	400067	32 - 35 mm	25	M8, M10	20 mm	1.5 mm
SXD043	400068	40 - 43 mm	32	M8, M10	20 mm	1.5 mm
SXD052	400070	48 - 52 mm	40	M8, M10	20 mm	1.5 mm
SXD058	589350	54 - 58 mm		M8, M10	20 mm	2 mm
SXD061	400071	57 - 61 mm	50	M8, M10	20 mm	2 mm

物料号	订货号	外径 (OD)	NB/DN	杆尺寸 (RS)	宽度 (W)	厚度 (T)
SXD073	400073	70 - 73 mm		M8, M10	20 mm	2 mm
SXD080	400074	74 - 80 mm	65	M8, M10	20 mm	2 mm
SXD091	400075	83 - 91 mm	80	M8, M10	20 mm	2 mm
SXD114	400077	108 - 114 mm	100	M8, M10	23 mm	2 mm

Table 2/2				
物料号	订货号	螺钉直径 (Sc)	螺钉长度 (L)	静态负载
SXD014	400063	6	27mm	1000N
SXD019	400064	6	27mm	1000N
SXD023	400065	6	27mm	1000N
SXD028	400066	6	27mm	1000N
SXD035	400067	6	27mm	1000N
SXD043	400068	6	32mm	1000N
SXD052	400070	6	32mm	1300N
SXD058	589350	6	32mm	1300N
SXD061	400071	6	32mm	1300N
SXD073	400073	6	35mm	1300N
SXD080	400074	6	37mm	1300N
SXD091	400075	6	40mm	1300N
SXD114	400077	6	50mm	2200N

其他产品详情

Lining is EPDM rubber.



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

