

Universal Structural Bracket, Strut Brace

功能

Used for installations where strut brace is perpendicular to structure

One wrench size fits all required hardware, eliminating the need to change tools

Shear-off head helps ensure correct torque and simplifies inspection



材料: 钢
完成: 电镀锌



技术参数

Table 1/2

物料号	订货号	孔尺寸 (HS)	宽度 (W)	厚度 (T)	A	B
CSBUS1	404568	14.3 mm	40.6 mm	6.4 mm	133.4 mm	12.7 mm
CSBUS2	404569	20.6 mm	40.6 mm	6.4 mm	133.4 mm	12.7 mm

Table 2/2


物料号	订货号	C	D	E
CSBUS1	404568	40.6 mm	50.8 mm	66 mm
CSBUS2	404569	40.6 mm	50.8 mm	66 mm

其他产品详情

Cut length for strut member is +/- 1" (25 mm) of measured length.

FM Loads					
Part Number	Brace Member	Horizontal Capacity per Installation Angle from Vertical			
		30° - 44°	45° - 59°	60° - 74°	75° - 90°
CSBUS1	41 x 41 Strut Channel	8940 N	12630 N	15210 N	16940 N
CSBUS2	41 x 41 Strut Channel	8940 N	12630 N	15210 N	16940 N

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美 +1.800.753.9221 ， 按 1 转客户服务 ， 按 2 转技术支持	欧洲 荷兰： +31 800-0200135 法国： +33 800 901 793	欧洲 德国： 800 1890272 其他国家/地区： +31 13 5835404	亚太地区 上海： + 86 21 2412 1618/19 悉尼： +61 2 9751 8500
--	---	---	--

