


Wire Basket Tray Polymer Insert



The nVent CADDY Wire Basket Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray-providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

功能

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection

颜色: 黑色
材料: 聚合物

技术参数


Table 1/2

物料号	高度 (H)	宽度 (W)	长度 (L)	包含侧板	单位重量
WBTFORM04BA		92.2 mm	3048mm	否	0.02 kg
WBTFORM06BA		143 mm	3048mm	否	0.03 kg
WBTFORM08BA		193.8 mm	3048mm	否	0.04 kg
WBTFORM12BA		295.4 mm	3048mm	否	0.06 kg
WBTFORM16BA		397 mm	3048mm	否	0.08 kg
WBTFORM18BA		447.8 mm	3048mm	否	0.09 kg
WBTFORM20BA		498.6 mm	3048mm	否	0.1 kg
WBTFORM24BA		600.2 mm	3048mm	否	0.12 kg
WBTFORM2X12BA	50.8 mm	295.4 mm	3048mm	是	0.08 kg
WBTFORM2X16BA	50.8 mm	397 mm	3048mm	是	0.1 kg

物料号	高度 (H)	宽度 (W)	长度 (L)	包含侧板	单位重量
WBTFORM2X18BA	50.8 mm	447.8 mm	3048mm	是	0.11 kg
WBTFORM2X20BA	50.8 mm	498.6 mm	3048mm	是	0.12 kg
WBTFORM2X24BA	50.8 mm	600.2 mm	3048mm	是	0.14 kg
WBTFORM2X4BA	50.8 mm	92.2 mm	3048mm	是	0.04 kg
WBTFORM2X6BA	50.8 mm	143 mm	3048mm	是	0.05 kg
WBTFORM2X8BA	50.8 mm	193.8 mm	3048mm	是	0.06 kg
WBTFORM4X12BA	101.6 mm	295.4 mm	3048mm	是	0.1 kg
WBTFORM4X16BA	101.6 mm	397 mm	3048mm	是	0.12 kg
WBTFORM4X18BA	101.6 mm	447.8 mm	3048mm	是	0.13 kg
WBTFORM4X20BA	101.6 mm	498.6 mm	3048mm	是	0.14 kg

Table 2/2

物料号	高度 (H)	宽度 (W)	长度 (L)	包含侧板	单位重量
WBTFORM4X24BA	101.6 mm	600.2 mm	3048mm	是	0.16 kg
WBTFORM4X4BA	101.6 mm	92.2 mm	3048mm	是	0.06 kg
WBTFORM4X6BA	101.6 mm	143 mm	3048mm	是	0.07 kg
WBTFORM4X8BA	101.6 mm	193.8 mm	3048mm	是	0.08 kg
WBTFORM6X12BA	152.4 mm	295.4 mm	3048mm	是	0.12 kg
WBTFORM6X16BA	152.4 mm	397 mm	3048mm	是	0.14 kg
WBTFORM6X18BA	152.4 mm	447.8 mm	3048mm	是	0.16 kg
WBTFORM6X20BA	152.4 mm	498.6 mm	3048mm	是	0.18 kg
WBTFORM6X24BA	152.4 mm	600.2 mm	3048mm	是	0.18 kg
WBTFORM6X8BA	152.4 mm	193.8 mm	3048mm	是	0.1 kg



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221

，按 1 转客户服务

，按 2 转技术支持

欧洲

荷兰：

+31 800-0200135

法国：

+33 800 901 793

欧洲

德国：

800 1890272

其他国家/地区：

+31 13 5835404

亚太地区

上海：

+ 86 21 2412 1618/19

悉尼：

+61 2 9751 8500

