

钢板门，DN

该门取代落地式机柜中的后背板，以使用户从后部操作安装设备，或使用背靠背安装板来增大机柜的安装空间。



功能

Description: Standard door equipped with double-bit 3 mm lock system and door frame. Door accessory kit DNМК (hinges, rod catches) to be ordered separately. Allows all the options of the locking program and 180° hinges. Compatible with combinable and compact enclosure ranges.

Material: 2 mm steel plate.

Maximum load: 800 N.

Finish: RAL 7035 structured powder coating.

Mounting requirements: Use hinge kit DNМК if no door was fitted previously.

Pack quantity: 1 piece.

材料:	低碳钢
完成:	粉末涂层
颜色:	浅灰色
颜色代码:	RAL 7035
厚度:	2mm

技术参数

Table 1/2

物料号	订货号	高度	宽度	深度	门类型	产品系列
DN1406R5	DN1406R5	1382mm	593mm	17mm	普通	独立
DN1408R5	DN1408R5	1382mm	793mm	17mm	普通	独立
DN1606LR5	DN1606LR5	1582mm	593mm	17mm	左门	独立
DN1606R5	DN1606R5	1582mm	593mm	17mm	普通	独立
DN1606RR5	DN1606RR5	1582mm	593mm	17mm	右门	独立
DN1608R5	DN1608R5	1582mm	793mm	17mm	普通	独立
DN1610R5	DN1610R5	1582mm	993mm	17mm	普通	独立
DN1804LR5	DN1804LR5	1782mm	393mm	17mm	左门	独立
DN1804RR5	DN1804RR5	1782mm	393mm	17mm	右门	独立
DN1805LR5	DN1805LR5	1782mm	493mm	17mm	左门	独立
DN1805R5	DN1805R5	1782mm	493mm	17mm	普通	独立
DN1805RR5	DN1805RR5	1782mm	493mm	17mm	右门	独立
DN1806LR5	DN1806LR5	1782mm	593mm	17mm	左门	独立
DN1806R5	DN1806R5	1782mm	593mm	17mm	普通	独立
DN1806RR5	DN1806RR5	1782mm	593mm	17mm	右门	独立
DN1808LR5	DN1808LR5	1782mm	793mm	17mm	左门	独立
DN1808R5	DN1808R5	1782mm	793mm	17mm	普通	独立
DN1808RR5	DN1808RR5	1782mm	793mm	17mm	右门	独立
DN1810R5	DN1810R5	1782mm	993mm	17mm	普通	独立
DN2004LR5	DN2004LR5	1982mm	393mm	17mm	左门	独立

Table 2/2

物料号	订货号	高度	宽度	深度	门类型	产品系列
DN2004RR5	DN2004RR5	1982mm	393mm	17mm	右门	独立
DN2005LR5	DN2005LR5	1982mm	493mm	17mm	左门	独立
DN2005R5	DN2005R5	1982mm	493mm	17mm	普通	独立
DN2005RR5	DN2005RR5	1982mm	493mm	17mm	右门	独立
DN2006LR5	DN2006LR5	1982mm	593mm	17mm	左门	独立
DN2006R5	DN2006R5	1982mm	593mm	17mm	普通	独立
DN2006RR5	DN2006RR5	1982mm	593mm	17mm	右门	独立
DN2008LR5	DN2008LR5	1982mm	793mm	17mm	左门	独立
DN2008R5	DN2008R5	1982mm	793mm	17mm	普通	独立

物料号	订货号	高度	宽度	深度	门类型	产品系列
DN2008RR5	DN2008RR5	1982mm	793mm	17mm	右门	独立
DN2010R5	DN2010R5	1982mm	993mm	17mm	普通	独立
DN2205LR5	DN2205LR5	2182mm	493mm	17mm	左门	独立
DN2205RR5	DN2205RR5	2182mm	493mm	17mm	右门	独立
DN2206LR5	DN2206LR5	2182mm	593mm	17mm	左门	独立
DN2206R5	DN2206R5	2182mm	593mm	17mm	普通	独立
DN2206RR5	DN2206RR5	2182mm	593mm	17mm	右门	独立
DN2208R5	DN2208R5	2182mm	793mm	17mm	普通	独立

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

