

# 侧板，SPM

用以密封机柜两侧，保护电气组件在没有任何干扰的情况下运行，并防止人员受伤害。

## 功能

Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws and new patented retainers. Can be replaced by the side door DNS.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: IP 55, TYPE 12, 13 in combination with MCS.  
IP66, TYPE 4, 12, 13 in combination with MCS-HP.

Pack quantity: 2 panels with mounting accessories.

完成: 粉末涂层  
颜色: 浅灰色  
颜色代码: RAL 7035  
厚度: 1.5mm

## 技术参数

| 物料号       | 订货号       | 高度     | 宽度   | 深度    | 产品系列 | 外壳材料 |
|-----------|-----------|--------|------|-------|------|------|
| SPM1805R5 | SPM1805R5 | 1800mm | 19mm | 500mm | 独立   | 低碳钢  |
| SPM1804R5 | SPM1804R5 | 1800mm | 19mm | 400mm | 独立   | 低碳钢  |
| SPM1806R5 | SPM1806R5 | 1800mm | 19mm | 600mm | 独立   | 低碳钢  |
| SPM2005R5 | SPM2005R5 | 2000mm | 19mm | 500mm | 独立   | 低碳钢  |
| SPM2004R5 | SPM2004R5 | 2000mm | 19mm | 400mm | 独立   | 低碳钢  |
| SPM2006R5 | SPM2006R5 | 2000mm | 19mm | 600mm | 独立   | 低碳钢  |
| SPM2008R5 | SPM2008R5 | 2000mm | 19mm | 800mm | 独立   | 低碳钢  |
| SPM2206R5 | SPM2206R5 | 2200mm | 19mm | 600mm | 独立   | 低碳钢  |
| SPM2208R5 | SPM2208R5 | 2200mm | 19mm | 800mm | 独立   | 低碳钢  |

| 物料号       | 订货号       | 高度     | 宽度   | 深度    | 产品系列 | 外壳材料 |
|-----------|-----------|--------|------|-------|------|------|
| SPM1406R5 | SPM1406R5 | 1400mm | 19mm | 600mm | 独立   | 低碳钢  |
| SPM1606R5 | SPM1606R5 | 1600mm | 19mm | 600mm | 独立   | 低碳钢  |
| SPM1808R5 | SPM1808R5 | 1800mm | 19mm | 800mm | 独立   | 低碳钢  |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

