


车载机架



适合持续振动、冲击、高温和高湿度环境。

功能

- 适用于移动铁路应用
- 可用于持续振动, 冲击, 高温, 和高湿度环境
- 适用于 1, 2, 或 3 U SNCF 插箱 (NF F61-005, CF 60-002)
- 后侧配有标准连接器; 横杆可以针对 SNCF 编码销进行自定义编码
- 横杆带有集成电缆槽
- 多个机架可以彼此叠加或并排放置
- 使用焊接工艺生产, 获得 EN 15085 (CL2) 认证
- 不锈钢焊缝钝化, 防止腐蚀

- 深度: 341.8mm
- 完成: 未加工
- 符合: SNCF NFF 61005; SNCF NFF 60002
- 框架材料: 不锈钢
- 静态负载: 25kg
- 产品类型: 机架



技术参数

物料号	机架高度	高度	宽度	包装数量	材料	机架宽度
10170-012	6U	290mm	496.4mm	1	不锈钢	84HP
10170-013	6U	290mm	252.65mm	1	不锈钢	36HP
10170-014	3U	156.7mm	496.4mm	1	不锈钢	84HP
10170-015	3U	156.7mm	252.65mm	1	不锈钢	36HP
10170-016	9U	423.4mm	496.4mm	1	不锈钢	84HP
10170-017	9U	423.4mm	252.65mm	1	不锈钢	36HP

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

