

# 凸缘螺钉, 滚花头短版



Integrated load spreading, replaces separate washer.  
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

## 功能

凸缘螺钉, 滚花头短版

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

产品类型: 螺钉  
类型: 螺钉  
搭配: 前面板



## 技术参数

Table 1/2

| 物料号       | 长度     | 材料 | 完成 | 包装数量 | 螺纹尺寸 | 深度     |
|-----------|--------|----|----|------|------|--------|
| 21101-749 | 12.3mm | 黄铜 | 镀镍 | 100  | M2.5 | 18.3mm |
| 21100-268 | 11mm   | 黄铜 | 镀镍 | 100  | M2.5 |        |
| 21101-106 | 11mm   | 钢  |    |      | M2.5 |        |

Table 2/2

| 物料号       | 高度  | 宽度  | 螺纹长度   | 扭矩        | 认证   |
|-----------|-----|-----|--------|-----------|------|
| 21101-749 | 8mm | 8mm | 12.3mm | 0.3N · m  | RoHS |
| 21100-268 |     |     |        | 0.22N · m |      |
| 21101-106 |     |     |        | 0.22N · m |      |

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

