


压铸支脚



铝压铸材料制成的翻转式支脚可以安装在机箱底板上。带或不带翻转功能。颜色 RAL 9006 白色铝色。

功能

防滑橡胶块将机箱固定到位

可用于替代标准支脚

承载能力：50 千克/英尺, 最大机箱重量：40 千克

机箱底盖上有安装孔

- 颜色: 银色
- 材料: 铝
- 产品系列: RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
- 产品类型: 支脚
- 搭配: 仪器箱



技术参数

物料号	包装数量	颜色代码	类型
10603-001	1	RAL 9006	支脚, 不带翻转功能
10603-002	1	RAL 9006	支脚, 带翻转功能

其他产品详情

以多个标准包装的形式交货。以单件为单位定价。

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent

的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

