

Varistar CP LHX+ Cabinet, 10 KW, RAL 7021, EMC, 42 U, 2100H, 600W, 1000深

??

物料号

10630-053

Varistar CP LHX + liquid cooled cabinets are designed to deliver localized energy efficient cooling to the equipment in installations where the ambient air is not filtered or temperature controlled. It incorporates an LHX5 / LHX10 cooler fitted in the bottom directly on the 19" uprights. Warm air is pulled from the rear plenum of the cabinet, cooled in the air / liquid heat exchanger, and supplied into the front plenum. The sealed cabinet assures no air is exchanged with the ambient and the noise emissions remain at a low level.

功能

集成 LHX + 19" 机架冷却器的机柜, 冷却能力高达 10 kW, 温度精度为 $\Delta 0.1^\circ\text{K}$ 或 $^\circ\text{C}$

冷却装置安装在底部的 19 英寸立柱上, 控制器安装在顶部。柜内 35 U 可用空间

密封条可将 0.2 米距离处的噪音降低至 50.4 dB(A)

机柜具有高效电缆进线组件, 最小化对 IP 和 EMC 性能的影响

所有监控管理功能均可远程操作

最大静态承载能力 1600 千克

产品属性

机架高度: 42U

高度: 2100mm

宽度: 600mm

深度: 1000mm

框架颜色: 暗灰色

框架颜色代码: RAL 7021

覆层材料: 钢

覆层颜色: 暗灰色

覆层颜色代码: RAL 7021

包装数量: 1

符合: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-1

完成: 粉末涂层

框架材料: 钢

静态负载: 1600kg

材料: 钢

净重: 196.6kg

产品系列: Varistar CP

产品类型: 机柜

防护等级: IP55

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

