

IEL 型助插器/助拔器把手，IEL 型，黑色手柄，灰色按钮，顶部，100 个

物料号

20817-685

助拔器把手，IEL 型，符合 IEEE 1101.10 标准。0,1" 偏移。其中两个把手可以克服 700N 的单杠杆力（每对）。


功能

插入和拔出力高达 700 N（每对）

符合 IEEE 1101.10 和 IEC 60297-3-102 标准

可安装微型开关

0.1" 偏移用于带 背板贴片的 电源模块



产品属性

包装数量: 100

手柄类型: IEL; 顶部前部

可燃性等级: UL® 94V-0

颜色: 黑色

符合: EN 45545-2

材料: 聚碳酸酯; 锌合金

产品类型: 手柄

类型: 助插器/助拔器，0.1" 偏移

搭配: 前面板

毛重: 2.384kg

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

请单独订购编码键和微型开关。

Technical drawings of the 3D printer's extruder assembly, showing dimensions in millimeters.

Side View (Top Left): Shows the extruder's profile. Key dimensions include a total width of 35 mm, a mounting flange width of 26 mm, and a central shaft diameter of $\varnothing 2.95$ mm. Other dimensions include 2.5 mm, 6.1 mm, 3.6 mm, 2.5 mm, 3.8 mm, 8.55 mm, 8.15 mm, 12.75 mm, and 22.75 mm.

Bottom View (Bottom Left): Shows the extruder from below. Key dimensions include a total width of 20 mm, a central shaft diameter of $\varnothing 2.95$ mm, and a mounting flange width of 26 mm. Other dimensions include 2.54 mm, 6.61 mm, 2.54 mm, and 7.62 mm.

Top View (Bottom Right): Shows the extruder from above. Key dimensions include a total width of 20 mm, a central shaft diameter of $\varnothing 2.95$ mm, and a mounting flange width of 26 mm. Other dimensions include 2.54 mm, 6.61 mm, 2.54 mm, and 7.62 mm.

Isometric View (Top Right): A 3D perspective view of the extruder assembly, showing the extruder head, the mounting bracket, and the screws used for assembly.

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

