


机箱监测模块 CMM



??

物料号

23207-022

电压、温度和数字输入监测。

功能

数据总线 可与 SCHROFF 风扇控制模块 (FCM) 进行通信

可插拔，符合 3 U 欧洲电路板规格

支持 VME 和 CPCI 特定信号的输入和输出，
和其他数字输出和 LED 输出

通过 RS 232 或以太网接口 (10BaseT) 进行通信和远程控制

Status Monitor	Temp
Voltage	CMM [23] °C
+5.0V	FCM [24] °C
+12.0V	Fan Speed
+24.0V	[61] %
-24.0V	Fan Speed Setting
Temperature	T1 [25] °C
CMM	T2 [50] °C
FCM	Temp. Alarm
Fan Speed	CMM [40] °C
Fan 1	FCM [60] °C
Fan 2	
Fan 3	



产品属性

产品类型: 系统模块

*所示价格为每件价格，不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分，报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP)，即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中，因为运输时间可能会有所不同，具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品，在非推荐区域（“检测到的碰撞区域”）进行的开孔和修改可能会产生额外的工程和/或设计成本，这可能会增加最初的报价。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

