



		$\Delta R^+ =$ can be combined, ΔR^- combination not recommended			
Stange $\geq L$		-	+	+	+
		+	+	+	+
		+	+	+	+
Stange $< L$		+	+	-	-
		+	+	-	-
Dreiecksprofil		Light $\geq L$		Flachblech $\geq H$	
		Light $< L$		Flachblech $< H$	
		Light $\geq L$		Flachblech $\geq H$	
		Light $< L$		Flachblech $< H$	

34566-263

功能

铝挤压件, 阳极氧化, 接触表面导电, 带 HP 标记



净重: 0.2kg

nVent.com/SCHROFF | 1

其他产品详情

前端没有 M4 螺纹，无印刷，不带安装 19" 支架的槽口。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

