


适于背板的 EuropacPro 19 英寸插箱套件， 可加装电磁屏蔽功能

用于背板安装的非屏蔽型插箱。



功能

带 F 型（“灵活型”）侧板的插箱, 包含前 19 英寸法兰, 深度可调 19" 支架单独出售（交付的产品中不随附）

用于安装背板的后水平横梁，带绝缘条

铝结构

IP 20，符合 IEC 60529

提供改造，如开孔、各种表面或尺寸

扁平包装，节省空间

“轻”型水平横梁

内部和外部尺寸符合：IEC 60297-3-100, -101, IEEE 1101.1

EMC 屏蔽: 否

完成: 阳极氧化; 钝化

产品类型: 插箱/机箱



技术参数

Table 1/2						
物料号	机架高度	深度	包装数量	用于安装	板深度	垫片类型
24563-131	3U	175mm	1	背板	160mm	不锈钢 EMC（可改装）
24563-132	3U	235mm	1	背板	160mm, 220mm	不锈钢 EMC（可改装）
24563-133	3U	295mm	1	背板	160mm, 220mm, 280mm	不锈钢 EMC（可改装）
24563-134	3U	355mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）
24563-135	3U	415mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）
24563-136	3U	475mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）
24563-431	6U	175mm	1	背板	160mm	不锈钢 EMC（可改装）
24563-432	6U	235mm	1	背板	160mm, 220mm	不锈钢 EMC（可改装）
24563-433	6U	295mm	1	背板	160mm, 220mm, 280mm	不锈钢 EMC（可改装）
24563-434	6U	355mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）
24563-435	6U	415mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）
24563-436	6U	475mm	1	背板	160mm, 220mm, 280mm, 340mm	不锈钢 EMC（可改装）

Table 2/2						
物料号	包含手柄	安装	符合	材料	机架宽度	静态负载
24563-131	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-132	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-133	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-134	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-135	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-136	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-431	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-432	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-433	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-434	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-435	否	机架	IEC 60297-3-103	铝	84HP	11kg
24563-436	否	机架	IEC 60297-3-103	铝	84HP	11kg

其他产品详情

支持个性化配置: 支持较大范围高度，宽度和深度定制；根据不同应用可选多种规格导轨,内部附件和安装材料。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

