


前面板 EMC 不锈钢屏蔽套件



不锈钢
EMC垫片将插入屏蔽型前面板的横向插槽（每个前面板 2 件）。

- 功能
- 不锈钢 EMC
 - 垫片将插入屏蔽型前面板的横向插槽（每个前面板 2 件）
 - EMC 屏蔽条, 不锈钢

温度范围 -200°C - +160°C

材料: 不锈钢
产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; PropacPRO; 框架式插入单元
产品类型: 屏蔽套件
搭配: 插箱; 仪器箱; 前面板



技术参数


物料号	机架高度	包装数量	深度 (D)	高度 (H)	宽度 (W)
21101-705	3U	10	2.22mm	97mm	4.97mm
21101-707	6U	10	2.22mm		4.97mm
21101-706	3U	100	2.22mm	97mm	4.97mm
21101-708	6U	100			
21101-709	9U	10	2.22mm		4.97mm
21101-710	9U	100			
21101-713	4U	10	2.22mm	142mm	4.97mm
21101-714	4U	100			
21101-775	2U	10	2.22mm	52mm	4.97mm
21101-776	2U	100			
21101-777	5U	10			

物料号	机架高度	包装数量	深度 (D)	高度 (H)	宽度 (W)
21101-778	5U	100			

其他产品详情

请单独订购装配工具。

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

