

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

功能

新一代编码型塑料导轨，实现 PCB 或模件盒的可靠固定

稳定性显著提高, 得益于优化设计和高质量材料 (PC)

提高防火安全性能, 符合 EN 45545-2 规范 R22, R23 和 R24 中的最高危险等级 HL3

“无卤素”, 符合 IEC 61249-2-21 标准

导轨可以卡入水平横梁（铝挤压件）或 1.5 mm 厚板中

可以通过螺栓固定到 H 型和 R 型水平横梁，以满足更高的抗冲击和振动要求

可选 ESD 夹，用于 PCB 和水平横梁之间的导电触点

存储温度：从 -40 °C.. 130 °C

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac

产品类型: 导轨

类型: 编码

搭配: 插箱; 仪器箱; 19" 机箱; 系统



技术参数

物料号	板深度	槽宽	颜色	材料	包装数量	符合	完成
64568-089	160mm	2	红色	纤维增强型塑料	1	EN 45545-2	

物料号	板深度	槽宽	颜色	材料	包装数量	符合	完成
64568-090	160mm	2	灰色	纤维增强型塑料	1	EN 45545-2	
24568-331	280mm	2.5	红色, 银色	纤维增强型塑料, 铝	10	EN 45545-2	阳极氧化
24568-332	340mm	2.5	红色, 银色	纤维增强型塑料, 铝	10	EN 45545-2	阳极氧化
24568-341	280mm	2.5	灰色, 银色	纤维增强型塑料, 铝	10	EN 45545-2	阳极氧化
24568-342	340mm	2.5	灰色, 银色	纤维增强型塑料, 铝	10	EN 45545-2	
24568-356	160mm	2	红色	纤维增强型塑料	10	EN 45545-2	
24568-357	70mm	2	红色	纤维增强型塑料	10	EN 45545-2	
24568-358	160mm	2	灰色	纤维增强型塑料	10	EN 45545-2	
24568-360	70mm	2	灰色	纤维增强型塑料	10	EN 45545-2	
64568-085	70mm	2	红色	纤维增强型塑料	1	EN 45545-2	
64568-086	70mm	2	灰色	纤维增强型塑料	1	EN 45545-2	
64568-091	220mm	2	红色	纤维增强型塑料	1	EN 45545-2	
64568-092	220mm	2	灰色	纤维增强型塑料	1	EN 45545-2	
64568-111	220mm	2.5	红色, 银色	纤维增强型塑料, 铝	1	EN 45545-2	
64568-109	160mm	2.5	红色, 银色	纤维增强型塑料, 铝	1	EN 45545-2	
64568-110	160mm	2.5	灰色, 银色	纤维增强型塑料, 铝	1	EN 45545-2	
64568-112	220mm	2.5	灰色, 银色	纤维增强型塑料, 铝	1	EN 45545-2	

其他产品详情

请注意，交货数量会按照声明的标准包装量执行（例如，5 件、10 件、50 件等）我们会将不符合规定的订购数量（例如 2 件）更改为下一个可执行的标准包装量发货。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

