


电缆线

nVent SCHROFF
电源线可以通过实际、通用的方式用可变的连接设备紧固。
规格通用，适合不同的应用，如风扇、机柜灯、工业 PC 连接、不间断电源、系统等。



功能
应用：风扇, 机柜灯, 工业 PC 连接, 不间断电源和系统

产品类型： 电缆



技术参数

物料号	输入连接器	输出连接器	长度	包装数量	颜色	连接器类型	材料
60103-131	SCHUKO / UTE	IEC C13	2500mm	1	灰色	直向型	PVC
60103-137	BS = 英国标准	IEC C13	2500mm	1	黑色	直向型	PVC
60103-141	US = 美国标准	IEC C13	2500mm	1	黑色	直向型	PVC
60197-053	IEC C14	IEC C13	2500mm	1	黑色	直向型	PVC
60110-361	IEC C14	IEC C13	1000mm	1	黑色	直向型	PVC
60704-020	SCHUKO / UTE	IEC C13	2500mm	1	灰色	倾斜	PVC
62150-191	SCHUKO / UTE	IEC C13	2500mm	1	黑色	直向型	PVC
60110-360	IEC C14	IEC C13	500mm	1	黑色	直向型	PVC

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

