

盘头螺钉, Torx with Grounding


螺钉，垫片和螺母附件用于固定Subrack元器件

功能

固定Subrack元器件

Torx imprint bears greater torque

The star-shaped head prevents cam-out



完成: 镀锌
材料: 钢
产品系列: EuropacPRO
产品类型: 螺钉
类型: 盘头螺钉



技术参数

物料号	长度	包装数量	螺纹尺寸	搭配	螺纹长度	扭矩
24560-130	14mm	100	M4	插箱	14mm	1.2N · m
24560-131	14mm	10	M4	插箱	14mm	1.2N · m
24560-151	6mm	100	M4	插箱	6mm	1.2N · m
24560-155	10mm	100	M4	插箱	10mm	1.2N · m

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

