


盘头螺钉, Torx



盘头螺钉。

功能

盘头螺钉

The star-shaped head prevents cam-out

材料: 钢
产品类型: 螺钉
类型: 盘头螺钉



技术参数

Table 1/2

物料号	长度	完成	包装数量	螺纹尺寸	产品系列	搭配
24571-371	14m m	镀锌	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP
24571-372	10m m	镀锌	100	M4	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP
24560-148	10m m	镀镍	100	M2.5		背板, 测试适配器
24560-147	7mm	镀镍	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP
24560-135	6mm	镀锌	100	M4	EuropacPRO	插箱
24560-161	12m m	镀镍	100	M2.5		背板, 测试适配器

物料号	长度	完成	包装数量	螺纹尺寸	产品系列	搭配
24560-162	14mm	镀镍	100	M2.5		背板, 测试适配器
24560-163	16mm	镀镍	100	M2.5		背板, 测试适配器
24560-178	6mm	镀镍	100	M2.5	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO	前面板, Eurorack, Novastar, Varistar, Varistar CP

Table 2/2		
物料号	螺纹长度	扭矩
24571-371	14mm	1.2N • m
24571-372	10mm	1.2N • m
24560-148	10mm	0.3N • m
24560-147	7mm	0.3N • m
24560-135	6mm	1.2N • m
24560-161	12mm	0.3N • m
24560-162	14mm	0.3N • m
24560-163	16mm	0.3N • m
24560-178	6mm	0.3N • m

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

