

带 IET 把手的插入式模块, 屏蔽型, 黑色 3 U



模件盒, 带 IET 助插器/助拔器, 黑色把手, 3 U, 前组件。U 型前面板带 EMC导电布屏蔽条

功能

带EMC导电布屏蔽条的 U 型前面板

可承受高达 700 N 的插入力和拔出力 (每对)

可安装微型开关

可根据 IEC 60297-3-103/IEEE 1101.10 标准安装编码键

EMC 屏蔽: 是
完成: 阳极氧化; 钝化
材料: 铝
产品类型: 前面板
机架高度: 3U
类型: 带把手的前面板 (PIU)



技术参数

Table 1/2

物料号	机架宽度	包装数量	手柄类型	安装	垫片类型	正面表面处理
20848-763	4HP	1	IET	正面螺钉安装	织物 EMC	阳极氧化
20848-764	8HP	1	IET	正面螺钉安装	织物 EMC	阳极氧化
20848-765	12HP	1	IET	正面螺钉安装	织物 EMC	阳极氧化

Table 2/2

物料号	反面表面处理	边缘处理	符合	高度	宽度
20848-763	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	128.4mm	20mm

物料号	反面表面处理	边缘处理	符合	高度	宽度
20848-764	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	128.4m m	40.3m m
20848-765	碱蚀	否	IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11	128.4m m	60.6m m

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

