

Rail Wallmount SRW, EN50125-3 certified



Railway ready EN50125-3 vibration tested pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications.

功能

Finish: powder painting UV resistant

Body: Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting

Door: Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left opening with door stopper. Right opening doors available on request

Roof: Rain & Sun hood to protect against adverse weather conditions

Lock: Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking

Cable access: Gland plate on the bottom. Cut-outs can be requested based on project specific requirements

Protection: Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10

Internal accessories: Standard: Document Pocket A4; Optional: 19" uprights on the front, Mounting plate in the rear

External accessories: Optional: Lifting eyes, wall/pole mount kits

Additional information: For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration. The standard RWS enclosures are delivered with 2 pressure compensation breathers. One under the hood, one on the Gland plate. The pressure compensation breathers are also IP66.

Right opening doors available on request. Gland plate cutouts can be requested based on project specific requirements.

Optional: 19" uprights on the front, Mounting plate in the rear

技术参数

Table 1/2

物料号	机架高度	高度	宽度	深度	防护等级	颜色
SRW0604021	13U	600mm	400mm	210mm	IP66	浅灰色
SRW0606021	13U	600mm	600mm	210mm	IP66	浅灰色
SRW0606030	13U	600mm	600mm	300mm	IP66	浅灰色
SRW0806021	17U	800mm	600mm	210mm	IP66	浅灰色
SRW0806030	17U	800mm	600mm	300mm	IP66	浅灰色

Table 2/2

物料号	颜色代码	包装数量	符合	完成	框架材料
SRW0604021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	粉末涂层	不锈钢
SRW0606021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	粉末涂层	不锈钢
SRW0606030	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	粉末涂层	不锈钢
SRW0806021	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	粉末涂层	不锈钢
SRW0806030	RAL 7035	1	EN 50125-3, IEC 62262, IEC 60529	粉末涂层	不锈钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

