

300M Universal Beam Clamp, Plain, 17 mm Hole, 28 mm Max Flange



物料号

30017MM

功能

Universal beam clamp for standard beams

Structural attachment (with infinite adjustment) to top or bottom flange of metal beams to support hanger rod

Including set screw and lock nut



产品属性

订货号: 389505

材料: 铸铁

完成: 电镀锌

孔类型: 普通

孔尺寸 (HS): 17 mm

法兰厚度 (FT): 28 mm Max


A: 30 mm

扭矩 (TQ): 14 N • m Min

静态负载: 5500N

其他产品详情

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

