

# Branch Line Restraint Structure Attachment to Steel, M10, M12 Rod

## 物料号

**CSBBRS1MEG**

## 功能

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to steel members with self-drilling/tapping screw



## 产品属性

订货号: 402239

材料: 钢

完成: 电镀锌

杆尺寸 (RS): 10;12

法兰厚度 (FT): 2.7 - 12.7 mm

高度 (H): 28.2 mm

长度 (L): 40.4mm

宽度 (W): 26.9 mm


螺钉直径 (Sc): 2.7 mm

螺钉长度 (L): 32mm

其他产品详情

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221  
，按 1 转客户服务  
，按 2 转技术支持

欧洲

荷兰：  
+31 800-0200135  
法国：  
+33 800 901 793

欧洲

德国：  
800 1890272  
其他国家/地区：  
+31 13 5835404

亚太地区

上海：  
+ 86 21 2412 1618/19  
悉尼：  
+61 2 9751 8500

