

# Universal Restraint Clip, Slotted, #12, #18 Brace, M10 Rod



## 物料号

**CSBURCR38**

## 功能

Slotted design ideal for attaching to existing threaded rod on trapezes

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing



## 产品属性

订货号: 402201

材料: 钢

完成: 电镀锌

支架尺寸: #12;#18

杆尺寸 (RS): 10


厚度 (T): 4.27 mm

## 其他产品详情

Brace member is not included.

| UL Loads    |              |             |
|-------------|--------------|-------------|
| Part Number | Brace Member | Load Rating |
| CSBURCR38   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
| CSBURCR12   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |
| CSBURCR58   | CSB12CBL     | 1859 N      |
|             | CSB18CBL     | 3434 N      |

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221  
，按 1 转客户服务  
，按 2 转技术支持

欧洲

荷兰：  
+31 800-0200135  
法国：  
+33 800 901 793

欧洲

德国：  
800 1890272  
其他国家/地区：  
+31 13 5835404

亚太地区

上海：  
+ 86 21 2412 1618/19  
悉尼：  
+61 2 9751 8500

