

Beam Clamp, M6 Rod, 16 mm Max Flange



物料号

EBC

功能

Easy installation to beam flanges

One 10.5mm go-through hole allows the use of M6, M8 or M10 threaded rod, to attach any static load till 450N

Featuring three M6 threaded holes to attach electrical boxes directly to the side or bottom of the beam



产品属性

订货号: 170380

材料: 弹簧钢

完成: nVent CADDY 铠装

杆尺寸 (RS): 6

孔尺寸 (HS): 10.5 mm


法兰厚度 (FT): 16 mm Max

扭矩 (TQ): 3 N • m

静态负载: 450N

其他产品详情

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

