

nVent CADDY Pyramid Universal Support, 406 mm x 101.6 mm

物料号

PBU16M



功能

Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)

Base is manufactured from UV-stabilized thermoplastic material

产品属性

订货号: 360497

材料: 聚乙烯;聚丙烯;不锈钢 18-8 (EN 1.4305)

温度: -45 to 65 °C

静态负载安全系数: 3:1

长度 1 (L1): 406 mm

长度 2 (L2): 480 mm

高度 (H): 102 mm

宽度 (W): 201 mm

螺纹尺寸 (TS): M10




孔数量: 2

A: 165 mm

表面积: 91613mm²

静态负载: 6670N

单位重量: 1 kg



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

