

Rooftop Pyramid Equipment Support Kit, 6 Post Base, 2172 mm

物料号

PEK6B

功能

Kit includes post-base assemblies, frame and equipment-support clamps

Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated



产品属性

订货号: 360427

材料: 钢;聚丙烯;聚乙烯

完成: 热浸镀锌

温度: -34 to 54.4 °C

高度 (H): 305 - 457 mm

长度 (L): 2172mm


后基座 (A): 314 mm x 6 pc

方形管 (B): 1981 mm x 2 pc
横杆总成 (C): 1232 mm x 4 pc
宽度 (W): 1588 mm
表面积: 0.56m ²
单位重量: 56 kg
极限静态负载 (F): 9960N
静态负载安全系数: 3:1

其他产品详情

Static load must be stable and uniformly distributed across frame.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰:	德国:	上海:
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国:	其他国家/地区:	悉尼:
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

