

Rooftop Pyramid H-Frame Post Base, Foam

物料号

PHB

功能



Foam or rubber bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Rubber rooftop interface ideal for solar panel array installations

Mounting hardware pre-installed in bases

Hot-dip galvanized and UV stabilized for long lasting performance

Accepts standard strut channels

产品属性

订货号: 360422

材料: 钢;聚丙烯;聚乙烯

完成: 热浸镀锌

温度: -34 to 54.4 °C

静态负载安全系数: 3:1

屋顶接口: 泡沫

支柱类型: A (41 x 41 mm)

高度 (H): 117 mm

长度 (L): 314mm


宽度 (W): 314 mm

表面积: 0.09m²

单位重量: 1.8 kg

静态负载: 3335N

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

