

Rooftop Pyramid ST Adjustable Strut Support, 406 mm x 178–457 mm

物料号

PSA16AH18

功能



Height adjustability provides effective navigation of pipe, conduit, duct and cable tray around obstructions

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance

产品属性

订货号: 360469

材料: 聚乙烯;聚丙烯;钢

完成: 热浸镀锌

温度: -45 to 65 °C

静态负载安全系数: 3:1

长度 1 (L1): 406 mm

长度 2 (L2): 483 mm

高度 (H): 178 - 457 mm



宽度 (W): 203 mm

表面积: 91613mm²

单位重量: 3 kg

静态负载: 6670N

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

