

nVent CADDY Pyramid ST Bridge Assembly, 1,067 mm

物料号

PSB42A

功能

Ideal for supporting multiple pipe runs, cable tray and air handling units

Foam bottom offers low abrasion interface for better roof membrane protection


Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance



产品属性

订货号: 360478

材料: 聚乙烯;聚丙烯;钢

完成: 热浸镀锌

温度: -45 to 65 °C

静态负载安全系数: 3:1

长度 1 (L1): 1067 mm

长度 2 (L2): 1143 mm

高度 (H): 142 mm

宽度 (W): 203 mm

表面积: 183225mm²


单位重量: 4 kg

静态负载: 13340N

其他产品详情

Static loads are assumed to be uniformly distributed.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

