

# Speed Link For 2 mm Wire, 200 Pack

## 物料号

**SLK2C200**

## 功能

Push/pull keyless release allows easy adjustments

Low-profile locking device minimizes visual impact

Cable spread of 90 degrees allows positioning the device closer to the load

Keyless release tubes are easy to operate while wearing gloves

Double-sided locking mechanism enables simple height adjustment



## 产品属性

订货号: 196600

材料: 钢;聚丙烯;锌合金

钢丝绳直径: 1.5 - 2 mm

高度 (H): 55 mm


宽度 (W): 19 mm

厚度 (T): 12.5 mm

角度 (a): 90 ° Max

## 其他产品详情

Locking devices are only to be used with nVent CADDY Speed Link wire spools and accessories with the same specified Wire Rope Diameter as the locking device. Do not use with any other wires.



## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

### 北美

+1.800.753.9221  
，按 1 转客户服务  
，按 2 转技术支持

### 欧洲

荷兰：  
+31 800-0200135  
法国：  
+33 800 901 793

### 欧洲

德国：  
800 1890272  
其他国家/地区：  
+31 13 5835404

### 亚太地区

上海：  
+ 86 21 2412 1618/19  
悉尼：  
+61 2 9751 8500

