

I-Beam Attachment



功能

Snap-off bolt head helps enable easy installation and inspection of seismic sway braces

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing



技术参数

物料号	订货号	材料	完成	法兰厚度 (FT)	杆尺寸 (RS)	高度 (H)	宽度 (W)
CSBBC075EG	404350	铸铁	电镀锌	6.4 - 19.1 mm	0.5	63.5 mm	69.9 mm

其他产品详情

Structure Attachment and Brace Member are not included.

UL Loads				
Part Number	Structure Attachment Fitting	Flange Thickness	Brace Member	Load Rating
CSBBC075	CSBUNIV050	6 - 19 mm	DN25 - DN50 Sch. 40 NPS	3025 N
	CSBURC12	6 - 19 mm	CSB12CBL	1859 N
			CSB18CBL	3434 N
			CSB36CBL	3025 N
	CSBNPC12	6 - 19 mm	CSB12CBL	1859 N
			CSB18CBL	3434 N
			CSB36CBL	3025 N



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美 +1.800.753.9221 ， 按 1 转客户服务 ， 按 2 转技术支持	欧洲 荷兰： +31 800-0200135 法国： +33 800 901 793	欧洲 德国： 800 1890272 其他国家/地区： +31 13 5835404	亚太地区 上海： + 86 21 2412 1618/19 悉尼： +61 2 9751 8500
--	---	---	--

