


nVent CADDY Pyramid ST Bridge Assembly



功能

Ideal for supporting multiple pipe runs, cable tray and air handling units

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Ready to use out of the box, saving installation time and labor

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Hot-dip galvanized and UV stabilized for long lasting performance

材料: 聚乙烯;聚丙烯;钢
完成: 热浸镀锌
温度: -45 to 65 °C
静态负载安全系数: 3:1

技术参数

Table 1/2

物料号	订货号	长度 1 (L1)	长度 2 (L2)	高度 (H)	宽度 (W)	表面积
PSB24A	360475	610 mm	673 mm	142 mm	203 mm	118709mm ²
PSB42A	360478	1067 mm	1143 mm	142 mm	203 mm	183225mm ²

Table 2/2


物料号	订货号	单位重量	静态负载
PSB24A	360475	2 kg	8900N

物料号	订货号	单位重量	静态负载
PSB42A	360478	4 kg	13340N

其他产品详情

Static loads are assumed to be uniformly distributed.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

