

nVent CADDY Speed Link SLK with Angle Bracket



功能

Complete system includes wire, locking device and pre-assembled angle bracket end fitting

Ideal for attaching to concrete, steel or wood surfaces

Simple alternative to jack chain and additional hardware

材料: 钢; 锌合金; 聚丙烯
完成: 电镀锌
静态负载安全系数: 5:1
符合: SMACNA HVAC-DCS



技术参数

Table 1/2


物料号	订货号	钢丝绳直径	钢丝绳长度	A	孔尺寸 (HS)	高度 (H)
SLK2L3AB	196530	2 mm	3m	22.6 mm	7.1 mm	55 mm
SLK2L5AB	196531	2 mm	5m	22.6 mm	7.1 mm	55 mm
SLK3L10AB	196716	3 mm	10m	22.6 mm	7.1 mm	62 mm

Table 2/2

物料号	订货号	宽度 (W)	厚度 (T)	角度 (a)	静态负载	认证
SLK2L3AB	196530	19 mm	12.5 mm	90 ° Max	440N	cUL, ITB, UL
SLK2L5AB	196531	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, ITB

物料号	订货号	宽度 (W)	厚度 (T)	角度 (a)	静态负载	认证
SLK3L10AB	196716	24 mm	16 mm	90 ° Max	890N	

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

