

SCH2 Single Piece Strut Clamp for Cable/Conduit



功能

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel

FM® Specification Tested (from 1/2" to 4" of EMT Conduit Size)

材料: 钢
完成: 电镀锌




技术参数

物料号	外径 (OD)	静态负载 1 (F1)	极限静态负载 2 (F2)	极限静态负载 3 (F3)	认证
SCH12B	14.5 - 23.4 mm	880N	334N	222N	UL, OSHPD/HCAI, cUL
SCH16B	18.3 - 29.5 mm	880N	334N	222N	cUL, UL, OSHPD/HCAI
SCH20B	25.4 - 38.4 mm	880N	334N	222N	cUL, UL, OSHPD/HCAI
SCH24B	31.8 - 44.2 mm	1550N	334N	222N	cUL, UL, OSHPD/HCAI
SCH32B	44.2 - 55.9 mm	1550N	334N	222N	UL, OSHPD/HCAI, cUL
SCH40B	50.8 - 60.5 mm	1550N	334N	222N	OSHPD/HCAI, cUL, UL
SCH48B	60.5 - 73.2 mm	1550N	334N	222N	OSHPD/HCAI, cUL, UL
SCH56B	69.1 - 88.9 mm	1550N	334N	222N	OSHPD/HCAI, cUL, UL
SCH64B	82.6 - 101.6 mm	1550N	334N	222N	OSHPD/HCAI, cUL, UL

物料号	外径 (OD)	静态负载 1 (F1)	极限静态负载 2 (F2)	极限静态负载 3 (F3)	认证
SCH6B	2.5 - 16 mm	880N	334N	222N	UL, cUL
SCH72B	97.8 - 114.3 mm	1550N	334N	222N	UL, cUL, OSHPD/HCAI
SCH8B	8.6 - 18 mm	880N	334N	222N	cUL, UL

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

