

Concept 双侧开门机柜



Concept Enclosures are ideal for machine control applications. With streamlined styling, flush quarter-turn latches and an attractive, durable finish. Two-door landscape models provide full-width access and easy panel installation.

工业标准

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997

维持 UL/CSA 外部安装要求所需的壁挂式托架。

NEMA/EEMAC Type 12

IP 55

IEC 60529, IP55

功能

满焊工艺，平滑打磨

角成型门

可以使用内置固定夹轻松拆卸和安装铰链销

门上配备高扭矩无螺纹螺柱和紧固件

外部成型法兰

面板安装螺柱适用于可选的 Concept 面板和其他附件

主体背面的安装孔用于可选外部壁挂式安装支架

带隐藏铰链的可拆卸门，样式简洁、美观

无缝 FIP 密封条

四分之一旋转开槽锁杆

60 英寸高机柜上有四个铰链

主体上的接地螺柱；门上的粘合装置

可选耐冲击非金属文件袋

五金套件包括面板安装螺母、面板接地五金件和密封垫圈

Minimum-width body flange provides maximum door opening (210 degrees)

Door opens 210 degrees

Door alignment device on doors wider than 30 in.

Installation instructions provided

Overlapping door design that provides full-width access

Three-point latch system on right-hand hinged door furnished with flush slotted insert

技术参数

物料号	订货号	高度	宽度	深度	材料	完成
CTD366012	77760	914mm	1524mm	305mm	低碳钢	粉末涂层

其他产品详情

请单独购买安装板。

有关热门的冷却产品和附件的信息，请参考规格表。

Optional NEMA-size panels require conversion kit Catalog Number CCPM4.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

