

Glazed Doors, ADCS



可在门关闭的情况下查看电气组件，避免频繁开关机柜。

功能

通过玻璃门，可以在机柜门关闭的情况下查看电气组件

用户无需打开机柜门即可监控元件的状态，从而保持侵入防护

Description: To replace the standard door, provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s)

Material: 1.5 mm AISI 304 stainless steel, 2 mm for enclosures with a height or width of 600 mm or greater and 4 mm clear safety glass

Finish: 400 pre-grained stainless steel

Protection: Complies with IP55, TYPE 12, 13, IK 07.

Pack quantity: 1 door

The glazed door allows the electrical components to be seen while the enclosure's door is closed

材料: 不锈钢 304

完成: 拉丝

厚度: 1.5mm

技术参数

物料号	高度	宽度	门锁数量	窗口大小	产品系列	外壳材料
ADCS03624	360mm	240mm	1	219 x 83mm	壁挂式安装	低碳钢
ADCS04030	400mm	300mm	1	259 x 143mm	壁挂式安装	低碳钢
ADCS04040	400mm	400mm	1	259 x 243mm	壁挂式安装	低碳钢
ADCS04060	400mm	600mm	1	259 x 443mm	壁挂式安装	低碳钢
ADCS05040	500mm	400mm	1	359 x 243mm	壁挂式安装	低碳钢
ADCS05050	500mm	500mm	1	359 x 343mm	壁挂式安装	低碳钢
ADCS06040	600mm	400mm	2	459 x 243mm	壁挂式安装	低碳钢
ADCS06060	600mm	600mm	2	459 x 443mm	壁挂式安装	低碳钢
ADCS06080	600mm	800mm	2	459 x 643mm	壁挂式安装	低碳钢
ADCS08060	800mm	600mm	2	659 x 443mm	壁挂式安装	低碳钢
ADCS08080	800mm	800mm	2	659 x 643mm	壁挂式安装	低碳钢
ADCS10080	1000mm	800mm	1	859 x 643mm	壁挂式安装	低碳钢
ADCS12080	1200mm	800mm	1	1059 x 643mm	壁挂式安装	低碳钢
ADCS14080	1400mm	800mm	1	1259 x 643mm	壁挂式安装	低碳钢

其他产品详情

产品

* 3 point espagnolette locking. Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

