

玻璃门，DNG

可在门关闭的情况下查看电气组件，避免频繁开关机柜。



功能

Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

材料: 低碳钢
完成: 粉末涂层
颜色: 浅灰色
颜色代码: RAL 7035
厚度: 2mm

技术参数

物料号	订货号	高度	宽度	深度	窗口大小	产品系列
DNG1106R5	DNG1106R5	1082mm	593mm	17mm	876 x 415mm	独立
DNG1206R5	DNG1206R5	1182mm	593mm	17mm	976 x 415mm	独立

物料号	订货号	高度	宽度	深度	窗口大小	产品系列
DNG1208R5	DNG1208R5	1182mm	793mm	17mm	976 x 615mm	独立
DNG1406R5	DNG1406R5	1382mm	593mm	17mm	1176 x 415mm	独立
DNG1408R5	DNG1408R5	1382mm	793mm	17mm	1176 x 615mm	独立
DNG1606R5	DNG1606R5	1582mm	593mm	17mm	1376 x 415mm	独立
DNG1608R5	DNG1608R5	1582mm	793mm	17mm	1376 x 615mm	独立
DNG1806R5	DNG1806R5	1782mm	593mm	17mm	1576 x 415mm	独立
DNG1808R5	DNG1808R5	1782mm	793mm	17mm	1576 x 615mm	独立
DNG2006R5	DNG2006R5	1982mm	593mm	17mm	1776 x 415mm	独立
DNG2008R5	DNG2008R5	1982mm	793mm	17mm	1776 x 615mm	独立
DNG2206R5	DNG2206R5	2182mm	593mm	17mm	1976 x 415mm	独立
DNG2208R5	DNG2208R5	2182mm	793mm	17mm	1976 x 615mm	独立

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

