

快装式安装轨，CLPF

The mounting profiles can be fixed in all directions, providing full flexibility for the mounting of accessories, components, and other equipment.

功能

Description: The CLPF profile system is a 40 mm wide and 25 mm high profile, which can be mounted in all directions on the enclosure's frame. It can also be used in combination with the CLPK and the VB profiles. By turning the profile it can be used as a standard CP20/40 profile in combination with GLM 40/6 sliding nut, to mount installation material which needs adjusting in depth. The profiles, when mounted onto the enclosure's frame are flush with the enclosure's profiles. Two rows of hole patterns for cage nut fixing and self tapping screws are provided. For 90 mm wide profiles two profiles can be mounted next to each other.

Material: Zinc plated steel.

Pack quantity: 4 profiles including snap-line for fixing.

材料: 低碳钢
完成: 镀锌
厚度: 1.5mm

技术参数

物料号	订货号	高度	宽度	深度	兼容的外壳高度	兼容的外壳宽度
CLPF1000	CLPF1000	40mm	925mm	25mm	1000mm min	1000mm min
CLPF1200	CLPF1200	40mm	1125mm	25mm	1200mm min	1200mm min
CLPF1400	CLPF1400	40mm	1325mm	25mm	1400mm min	1400mm min
CLPF1600	CLPF1600	40mm	1525mm	25mm	1600mm min	1600mm min
CLPF1800	CLPF1800	40mm	1725mm	25mm	1800mm min	1800mm min

物料号	订货号	高度	宽度	深度	兼容的外壳高度	兼容的外壳宽度
CLPF2000	CLPF2000	40mm	1925mm	25mm	2000mm min	2000mm min
CLPF2200	CLPF2200	40mm	2125mm	25mm	2200mm min	2200mm min
CLPF300		40mm	225mm	25mm	300mm min	300mm min
CLPF400	CLPF400	40mm	325mm	25mm	400mm min	400mm min
CLPF500	CLPF500	40mm	425mm	25mm	500mm min	500mm min
CLPF600	CLPF600	40mm	525mm	25mm	600mm min	600mm min
CLPF800	CLPF800	40mm	725mm	25mm	800mm min	800mm min

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

