


Stainless Steel Compact Version Single Door Enclosure, EKSS



The stainless steel single door compact floor standing enclosure range, EKSS, with a IP 66 protection degree, is available off the shelf in many different sizes. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure. This enclosure range is well suited for almost any environment, grade dependent.

工业标准

cULus_UL Listed

CE, UK CA, UL

IEC 61439

功能

Material: AISI 304 pre-grained stainless steel / AISI 316L. Body and removable rear panel: 1.5 mm. Door: 2 mm. Bottom plate: 1.5 mm. Mounting plate: 3 mm galvanized steel.

Body: One piece enclosure body. Integrated depth profiles with hole pattern, allowing mounting plate adjustable in depth.

Door: Surface mounted with 4 hinges allowing left or right hand opening. Including door frame with 25 mm hole pattern and earthing studs.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear door mounting.

Lock: External espagnolette 4-point locking system. Standard fitted double-bit 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

Bottom plates: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing.

Mounting plate: Double folded and slides into position. Adjustable in depth by steps of 25 mm with the MPD02 accessory. Mounting plate is supplied, attached on the outside of the enclosure packaging.

Earthing: Door is equipped with separate welded earthing studs and earthing to the frame can be accomplished by using the ECF.

Finish: 400 pre-grained stainless steel.

Protection: Complies with IP 66, TYPE 4X, 12, IK 10.

Delivery: One piece body with fitted door, bottom plate and mounting plate, including door earthing studs.
Delivered on a pallet which is identical to the width of the enclosure. Mounting plate is attached to the outside of the enclosure packaging. All the packing material is recyclable.

Bottom plates: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing

Mounting plate: Double folded and slides into position; adjustable in depth by steps of 25 mm with the MPD02 accessory; mounting plate is supplied, attached on the outside of the enclosure packaging

Earthing: Door is equipped with separate welded earthing studs and earthing to the frame can be accomplished by using the ECF


Delivery: One piece body with fitted door, bottom plate and mounting plate, including door earthing studs;
delivered on a pallet which is identical to the width of the enclosure; mounting plate is attached to the outside of the enclosure packaging; all the packing material is recyclable

完成: 拉丝
主体厚度: 1.5mm
门厚: 2mm

技术参数

物料号	高度 (H)	宽度 (W)	深度 (D)	材料	面板尺寸	重量
EKSS14084	1400mm	800mm	400mm	不锈钢 304	1294 x 694mm	89kg
EKSS14084-316	1400mm	800mm	400mm	不锈钢 316L	1294 x 694mm	89kg
EKSS16064	1600mm	600mm	400mm	不锈钢 304	1494 x 494mm	84kg
EKSS16064-316	1600mm	600mm	400mm	不锈钢 316L	1494 x 494mm	84kg
EKSS16084	1600mm	800mm	400mm	不锈钢 304	1494 x 694mm	102kg
EKSS16084-316	1600mm	800mm	400mm	不锈钢 316L	1494 x 694mm	102kg
EKSS16104	1600mm	1000mm	400mm	不锈钢 304	1494 x 894mm	123kg
EKSS16104-316	1600mm	1000mm	400mm	不锈钢 316L	1494 x 894mm	123kg
EKSS18064	1800mm	600mm	400mm	不锈钢 304	1694 x 494mm	97kg
EKSS18064-316	1800mm	600mm	400mm	不锈钢 316L	1694 x 494mm	97kg
EKSS18084	1800mm	800mm	400mm	不锈钢 304	1694 x 694mm	117kg
EKSS18084-316	1800mm	800mm	400mm	不锈钢 316L	1694 x 694mm	117kg
EKSS18104	1800mm	1000mm	400mm	不锈钢 304	1694 x 894mm	138kg
EKSS18104-316	1800mm	1000mm	400mm	不锈钢 316L	1694 x 894mm	138kg
EKSS20084	2000mm	800mm	400mm	不锈钢 304	1894 x 694mm	127kg

物料号	高度 (H)	宽度 (W)	深度 (D)	材料	面板尺寸	重量
EKSS20084-316	2000mm	800mm	400mm	不锈钢 316L	1894 x 694mm	127kg
EKSS20104	2000mm	1000mm	400mm	不锈钢 304	1894 x 894mm	152kg
EKSS20104-316	2000mm	1000mm	400mm	不锈钢 316L	1894 x 894mm	152kg



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

