

Stainless Steel Glazed Doors, DNGS



Electrical components can be viewed while the transparent stainless steel door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

功能

Description: Transparent door fitted with clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking programme.

Material: Frame: 2 mm AISI 304 stainless steel plate, AISI 316L (on request). Viewing area: 4 mm clear safety glass.

Finish: 400 pre-grained stainless steel.

Protection: IP 55, TYPE 12, 13, IK 07.

Mounting requirements: Use hinge kit DNMKS01 if not for replacement of standard door.

Pack quantity: 1 piece.

材料: 不锈钢 304

完成: 拉丝

厚度: 2mm

技术参数

物料号	高度	宽度	深度	窗口大小	产品系列	外壳材料
DNGS1408	1400mm	800mm	17mm	1176 x 615mm	独立	低碳钢
DNGS1606	1600mm	600mm	17mm	1376 x 415mm	独立	低碳钢
DNGS1608	1600mm	800mm	17mm	1376 x 615mm	独立	低碳钢
DNGS1610	1600mm	1000mm	17mm	1376 x 815mm	独立	低碳钢

物料号	高度	宽度	深度	窗口大小	产品系列	外壳材料
DNGS1806	1800mm	600mm	17mm	1576 x 415mm	独立	低碳钢
DNGS1808	1800mm	800mm	17mm	1576 x 615mm	独立	低碳钢
DNGS1810	1800mm	1000mm	17mm	1576 x 815mm	独立	低碳钢
DNGS2006	2000mm	600mm	17mm	1776 x 415mm	独立	低碳钢
DNGS2008	2000mm	800mm	17mm	1776 x 615mm	独立	低碳钢
DNGS2010	2000mm	1000mm	17mm	1776 x 815mm	独立	低碳钢

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

