

Window Door, ADT

可在门关闭的情况下查看电气组件，避免频繁开关机柜。

功能

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 3 mm transparent acrylic glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP55, IK 07.

Pack quantity: 1 door.

材料: 低碳钢
完成: 粉末涂层
颜色: 浅灰色
颜色代码: RAL 7035

技术参数

物料号	订货号	高度	宽度	深度	厚度	门锁数量
ADT03025R5	ADT03025R5	295mm	245mm	15mm	1.2mm	1
ADT03030R5	ADT03030R5	295mm	294mm	15mm	1.2mm	1
ADT04030R5	ADT04030R5	395mm	294mm	15mm	1.2mm	1
ADT04040R5	ADT04040R5	395mm	394mm	15mm	1.2mm	1
ADT05030R5	ADT05030R5	495mm	294mm	15mm	1.5mm	1
ADT05040R5	ADT05040R5	495mm	394mm	15mm	1.5mm	1
ADT06040R5	ADT06040R5	595mm	394mm	15mm	1.5mm	2
ADT06050R5	ADT06050R5	595mm	495mm	15mm	1.5mm	2

物料号	订货号	高度	宽度	深度	厚度	门锁数量
ADT06060R5	ADT06060R5	595mm	595mm	15mm	1.5mm	2
ADT07050R5	ADT07050R5	695mm	495mm	15mm	1.5mm	2
ADT08060R5	ADT08060R5	795mm	595mm	15mm	2mm	2
ADT10060R5	ADT10060R5	995mm	595mm	15mm	2mm	1
ADT10080R5	ADT10080R5	995mm	795mm	15mm	2mm	1
ADT12060R5	ADT12060R5	1195mm	595mm	15mm	2mm	1
ADT12080R5	ADT12080R5	1195mm	795mm	15mm	2mm	1

其他产品详情

* 3 point espagnolette locking. Not suitable for AFS.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

