


凸缘螺钉, 十字槽/开槽



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

功能

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

产品类型: 螺钉

类型: 螺钉



技术参数

Table 1/3

物料号	直径	长度	材料	完成	包装数量	螺纹尺寸
21101-101		12.3mm	钢	镀镍	100	M2.5
21101-906		12.3mm	不锈钢		100	M2.5
21101-102		12.3mm	钢	Zinc Plated, Black	100	M2.5
21101-323		11mm			100	M2.5
21102-026	2.5mm	12.3mm	钢	镀镍	100	M2.5

Table 2/3

物料号	深度	高度	宽度	搭配	螺纹长度	螺纹类型
21101-101	14.3mm	5mm	5mm	前面板	12.3mm	公制
21101-906				前面板	12.3mm	
21101-102	14.3mm	5mm	5mm	前面板	12.3mm	公制

物料号	深度	高度	宽度	搭配	螺纹长度	螺纹类型
21101-323				前面板		
21102-026				框架式插入单元, 模件盒	3mm	

Table 3/3		
物料号	扭矩	认证
21101-101	0.3N • m	RoHS
21101-906	0.3N • m	RoHS
21101-102	0.3N • m	RoHS
21101-323	0.3N • m	
21102-026	0.3N • m	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

