

凸缘螺钉, 滚花头短版



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

功能

凸缘螺钉, 滚花头短版

For EuropacPRO and RatiopacPRO

Knurled head for manual screwing / unscrewing

产品类型: 螺钉
类型: 螺钉
搭配: 前面板



技术参数

Table 1/2

物料号	长度	材料	完成	包装数量	螺纹尺寸	深度
21101-749	12.3mm	黄铜	镀镍	100	M2.5	18.3mm
21100-268	11mm	黄铜	镀镍	100	M2.5	
21101-106	11mm	钢			M2.5	

Table 2/2

物料号	高度	宽度	螺纹长度	扭矩	认证
21101-749	8mm	8mm	12.3mm	0.3N · m	RoHS
21100-268				0.22N · m	
21101-106				0.22N · m	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

