


沉头螺钉，内梅花



用螺钉或铆钉固定到 PCB。

功能

适合用螺钉固定插箱或机箱附件

Torx imprint bears greater torque

The star-shaped head prevents cam-out

产品系列: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO

产品类型: 螺钉

类型: 沉头螺钉



技术参数

Table 1/2

物料号	长度	材料	完成	包装数量	螺纹尺寸	搭配
24560-146	5mm	钢	镀锌	100	M2.5	插箱, 仪器箱, 机箱
24571-373	8mm	钢	镀镍	100	M4	RatiopacPRO

Table 2/2

物料号	螺纹长度	扭矩	认证
24560-146	5mm	0.3N · m	RoHS
24571-373	8mm	1.2N · m	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

