


适于 FMC 夹层前面板开孔的边框, VITA 57.1



物料号

20835-849

FMC 面板安装在支持 FMC 夹层卡开孔的前面板中, 10 个 FMC 面板组成的套件。

功能

FMC 面板可以安装在支持 FMC 夹层板开孔的前面板中

FMC 面板可以选择使用导电 O 形圈屏蔽, 请单独订购

材料, 铝挤压件 (阳极氧化, 表面导电)



产品属性

产品类型: 前面板

类型: 夹层前面板

附件类型: 前面板

安装: 卡扣嵌入式

EMC 屏蔽: 无 (可改装)

垫片类型: O 形环 EMC

材料: 铝

正面表面处理: 阳极氧化

反面表面处理: 导电

边缘处理: 否

高度: 58.45mm

宽度: 12.8mm

深度: 2.5mm

符合: FMC Mezzanine; IEEE P1386

包装数量: 10

净重: 0.1kg

*所示价格为每件价格, 不含增值税。是否含包装费和运费取决于当地情况。如果这些费用应为总价的一部分, 报价中将包含包装费和运费。给定的价格为非约束性建议零售价 (RRP), 即 nVent 标价。当地经销商的最终销售价格可能会有所不同。在 SCHROFF.nVent.com 上请求或生成的报价仅对商业客户 (B2B) 有效。上面显示的交货时间是从 nVent SCHROFF 工厂发货该项目的估计值。运输时间不包括在此估计中, 因为运输时间可能会有所不同, 具体取决于送货地址、包裹尺寸和其他因素。对于配置的产品, 在非推荐区域 (“检测到的碰撞区域”) 进行的开孔和修改可能会产生额外的工程和/或设计成本, 这可能会增加最初的报价。

其他产品详情

请单独订购 EMC O 形圈。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书, 或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告, 可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

