


前把手,可改装，用于 RatiopacPRO



利用这款前把手，便于改装灵活且坚固的 RatiopacPRO/-
AIR 机箱，使操作更加轻松。

功能

用于改装带保护条的机箱，并用前把手替代

材料: 铝
产品类型: 手柄



技术参数

Table 1/2						
物料号	包装数量	手柄类型	颜色	完成	产品系列	类型
24571-301	2	前把手	灰色	粉末涂层	RatiopacPRO	静态
24571-302	2	前把手	灰色	粉末涂层	RatiopacPRO	静态
24571-303	2	前把手	灰色	粉末涂层	RatiopacPRO	静态
24571-304	2	前把手	灰色	粉末涂层	RatiopacPRO AIR	静态
24571-305	2	前把手	灰色	粉末涂层	RatiopacPRO AIR	静态
24571-306	2	前把手	灰色	粉末涂层	RatiopacPRO AIR	静态
24571-993	2	前把手	灰色	粉末涂层	RatiopacPRO	静态
24572-708	2			粉末涂层		

Table 2/2		
物料号	搭配	认证
24571-301	仪器箱, RatiopacPRO	RoHS

物料号	搭配	认证
24571-302	仪器箱, RatiopacPRO	RoHS
24571-303	仪器箱, RatiopacPRO	RoHS
24571-304	仪器箱, RatiopacPRO AIR	RoHS
24571-305	仪器箱	RoHS
24571-306	仪器箱	RoHS
24571-993	仪器箱, RatiopacPRO	RoHS
24572-708	仪器箱, RatiopacPRO	

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

