

前面板, 屏蔽型, 底部铰链固定

U 型底部铰链固定前面板，用于织物垫片。

功能

可在 135° 开口角度取下 U 型前面板的铰链（非 RatiopacPRO）

可以安装在水平轨道上

屏蔽型, U型前面板，带织物垫片

适用于插箱 (EuropacPRO) 和机箱 (RatiopacPRO), PropacPRO, CompacPRO)



- 附件类型: 前面板
- 深度 (D): 2.5mm
- 完成: 阳极氧化; 钝化
- 材料: 铝
- 产品类型: 前面板
- 类型: 不带把手的前面板



技术参数

Table 1/2						
物料号	机架高度	机架宽度	包装数量	安装	垫片类型	正面表面处理
20848-608	3U	28HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-599	3U	42HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-600	3U	63HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-601	3U	84HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-605	4U	42HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-606	4U	63HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-607	4U	84HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-604	6U	84HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-602	6U	42HP	1	铰链式，底部	织物 EMC	阳极氧化
20848-603	6U	63HP	1	铰链式，底部	织物 EMC	阳极氧化


物料号	机架高度	机架宽度	包装数量	安装	垫片类型	正面表面处理
20848-696	6U	28HP	1	铰链式，底部	织物 EMC	阳极氧化

Table 2/2						
物料号	反面表面处理	边缘处理	符合	EMC 屏蔽	高度 (H)	宽度 (W)
20848-608	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	128.4mm	141.9mm
20848-599	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	128.4mm	213mm
20848-600	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	128.4mm	319.7mm
20848-601	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	128.4mm	426.4mm
20848-605	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	172.9mm	213mm
20848-606	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	172.9mm	319.7mm
20848-607	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	172.9mm	426.4mm
20848-604	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	261.8mm	426.4mm
20848-602	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	261.8mm	213mm
20848-603	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	261.8mm	319.7mm
20848-696	导电	否	IEC 60297-3-101, IEEE 1101.1/10	无（可改装）	261.8mm	141.9mm

其他产品详情

可在打开位置 (> 135°)拆卸前面板。

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff

